

FEATURES

- Compact
- Used in a variety of applications
- Wide range of pressure measuring ranges
- High contrast display

RS PRO Digital Pressure Switch

RS Stock No.: 2351198



For Positive Pressure

With 2 Metre Lead

Product Description

Part No.	Port Size	Pressure Type
2351198	R1/8"	0.1 to 1 MPa

Features

- Compact
- Used in a wide variety of applications
- Wide range of pressure measuring ranges
- High contrast display

General Specifications

Maximum load current	80mA
Maximum applied voltage	28V
Repeatability	0.2% unit below the full scale
Working medium	Air, small combustion gas, noncorrosive gas
Display	4 positions, 7 segments display, R&B colour display
Display accuracy	+2% at full scale, +1% unit when at 25+3°C
Indicator light	1 output display green, 2 outputs. Display red
Enclosure rating	IP40
Operating temperature	Usage: 0°C to +50°C. Reserve: -10°C to +60°C (unfrozen)

Applicable Standards

CE, UL/CSA, RoHS

Similar Products

Part No.	Port Size	Pressure Type
2351193	R1/8"	0.1 to 1 MPa
2351199	R1/8"	0 to 101 KPa