



Live Date	Jan 6, 2014
Product Name	Corsair Flash Voyager USB3.0
Part Number	CMFVY3A-16GB, CMFVY3A-32GB, CMFVY3A-64GB, CMFVY3A-128GB
Product Image	
Tagline	Corsair's proprietary all-rubber housing is extremely durable, water resistant and drop-tested for worry-free transport of your valuable data
25 Words	Corsair USB 3.0 Flash Voyager flash drives offer up to 4x faster read speeds than traditional USB 2.0 drives in a rugged, reliable design with all-rubber housing.
50 Words	Get faster read speeds and rugged reliability with the Corsair Flash Voyager USB 3.0 flash drive. USB 3.0 read speeds let you access movies, pictures and large files up to 4x faster than traditional USB 2.0 drives and the durable rubber design is water resistant and shockproof to keep your data safe.
100 Words	<p>Fast – Access videos, pictures and large files up to 4x faster read speeds than traditional USB 2.0 drives</p> <p>Durable – Corsair's proprietary all-rubber housing is extremely durable, water resistant and drop-tested for worry-free transport of your valuable data.</p> <p>Shock Proof – Solid state storage makes Flash Voyager drives virtual shock proof.</p> <p>Convenient – Just plug it in and go! Works with Windows, Mac OS X and even Linux without drivers.</p> <p>Compatible – Designed for USB 3.0, backward compatible with USB 2.0</p> <p>Backed by Corsair – A respected name with a passion for quality and customer service.</p>
Features	<ul style="list-style-type: none"> • Fast USB 3.0 connectivity • Durable rubber housing • Water resistant • Shock proof • Backward compatible with USB 2.0 • Plug-n-Play compatible • Compatible with Windows® 8, Windows 7, Windows Vista®, Windows XP, Mac OS, Linux



Corsair Flash Voyager® USB 3.0

CMFVY3A-16GB CMFVY3A-32GB

CMFVY3A-64GB CMFVY3A-128GB

Specification:

Corsair Part Numbers	UPC Code	Distributor/ Reseller MOQ	Unformatted Capacity *	Max Read	Max Write
CMFVY3A-16GB	843591047296	10	16GB	200MB/s	25MB/s
CMFVY3A-32GB	843591047302	10	32GB	200MB/s	40MB/s
CMFVY3A-64GB	843591047319	10	64GB	190MB/s	55MB/s
CMFVY3A-128GB	843591047289	5	128GB	190MB/s	60MB/s

Unit Dimension	2.87 x 0.91 x 0.58 inches (7.3 x 2.32 x 1.49cm)
Certification	CE, FCC, BSMI, C-Tick (RCM)
Operating Temperature	0° to 50°C

*Some of the listed capacity on a flash storage device is used for formatting and other functions and thus is not available for data storage. The actual available capacity for data storage is less than the capacity stated on the products.

Shipping Information:

Shipping Dimension	7.48 x 5.35 x 0.83 inches (19.0 x 13.6 x 2.1 cm)	Master Pack Dimension	16.42 x 12.52 x 18.43 inches (41.7 x 31.8 x 46.8 cm)
Shipping Weight	0.137 lb (0.062kg)	Master Pack	19.97 lbs
Unboxed Product Weight	0.055 lb (0.025kg)	Weight	9.06 kg
Inner Pack Quantity	20	Harmonized Tariff Code	8471.70.6000
Inner Pack Dimension	11.77 x 7.83 x 5.70 inches (29.9 x 19.9 x 14.5 cm)	Country of Origin	Taiwan
Inner Pack Weight	3.064 lbs (1.39kg)	Warranty	Five Years