



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/50-60Hz 60S min.
操作力 Operation force	≤180±30gf / ≥250±50gf
寿命试验 Operating Life	50,000 cycles / 30,000 cycles
行程 Travels	0.25±0.1mm

PRODUCT NO. : 1TS002*****-CT

- 轻触开关
- 3X6系列
- 外形:
 - A=插脚
 - B=贴片
 - C=贴片带柱
 - K=贴片带柱8.8
 - L=贴片10.2
- 按钮颜色:
 - 底座颜色:
 - 盖板颜色:
- 操作力度:
 - 130=130gf
 - 160=160gf
 - 180=180gf
 - 250=250gf
 - 300=300gf
- 手感:
 - 0=带规
 - 1=大手感
 - 2=小手感
 - 3=特殊手感
- 材质:
 - 0=初始材质
 - 1=新增材质
 - 依次增加
- 产品高度(H):
 - 350=3.5mm
 - 370=3.7mm
- 非编带
- 编带, 不启用

RECOMMENDED P.C.B. LAYOUT
安装尺寸图

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	STAINLESS STEEL	/
4	ACTUATOR	1	LCP	BLACK
3	DOME	1	STAINLESS STEEL	AG-PLATED
2	TERMINAL	2	BRASS	AG-PLATED
1	HOUSING	1	LCP	YELLOW

X. ± 0.3	X. ± 3'	UNITS	MM
.X ± 0.2	.X' ± 2'	MAT'L	
.XX ± 0.1	.XX' ± 1'	FINISH	
.XXX ± 0.05	.XXX' ± 0.5'		

NAME(INTENDED USE)	HON YUAN
3X6 SMT SERIES	HON YUAN PRECISION IND. CO.,LTD.
TACT SWITCH	SHENZHEN, CHINA, R.O.C.
PART NO.(INTENDED USE)	TITLE:
ITS002G****-*****-CT*0	PRODUCT DRAWING
APPD: ZO 5/22/2014	DWG NO.: 1TS002G
CHKD: M.H.LI 5/22/2014	SCALE
DR: WP.LU 5/21/2014	10/1
	SHEET
	1/1
	REV.
	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.

REV	ECN NO.	APPD
A	HC-14-0007	PROUOM