


LOW-PROFILE SMT HEADER

(2.00 mm) .0787" PITCH • TMM SERIES



TMM

Board Mates:

CLT, SQT, SQW, ESQT, TLE, SMM, MMS

Cable Mates:

TCSD

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

Current Rating:

3.2 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

Voltage Rating:

281 VAC mated with SQW;
250 VAC mated with SQT

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*
*(.004" stencil solution may be available; contact IPG@samtec.com)

ALSO AVAILABLE

Other plating
(MOQ Required)



TMM	-	1	-	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	ROW OPTION	-	SM	-	OTHER OPTION
-----	---	---	---	------------------	---	------------	---	----------------	---	------------	---	----	---	--------------

02 thru 40

Specify LEAD STYLE from chart

-F
= Gold flash on post, Matte Tin on tail

-L
= 10 μ " (0.25 μ m) Gold on post, Matte Tin on tail

-S
= 30 μ " (0.76 μ m) Gold on post, Matte Tin on tail

-T
= Matte Tin

-S
= Single Row

-D
= Double Row


-A
= Alignment Pin (Metal or plastic at Samtec's discretion) (5 positions minimum) (-D only)

-"XXX"
= Polarized Position (Specify position of omitted pin)


-P
= Pick & Place Pad (3 positions minimum)

-TR
= Tape & Reel (3 thru 36 positions only)


-FR
= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (3 thru 36 positions only)



-P



LEAD STYLE	A	MATES WITH
-01	(3.20) .126	SQT, SQW, ESQT, TLE, SMM, MMS, TCSD
-04	(1.91) .075	CLT
-05	(1.65) .065	
-06	(4.27) .168	CLT-BE



-D

-S

Note:

Some lengths, styles and options are non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[TMM-104-01-L-D-RA](#) [TMM-103-03-G-S](#) [TMM-110-01-G-D](#) [TMM-110-01-S-D-RA](#) [TMM-132-03-S-D](#) [TMM-103-01-G-S-SM-P-TR](#) [TMM-128-03-S-D](#) [TMM-106-03-G-D](#) [TMM-104-01-L-D-SM](#) [TMM-102-01-S-D-RA](#) [TMM-102-02-G-S](#) [TMM-105-03-G-D](#) [TMM-108-01-L-D](#) [TMM-105-01-G-S-RA](#) [TMM-125-06-G-D-SM-P](#) [TMM-102-03-S-S](#) [TMM-105-01-L-D-SM-A](#) [TMM-108-01-S-D-RA](#) [TMM-102-01-G-S](#) [TMM-125-01-G-D](#) [TMM-117-03-G-S](#) [TMM-103-01-G-S](#) [TMM-103-01-G-D-SM-P-TR](#) [TMM-103-03-S-S](#) [TMM-105-03-G-S](#) [TMM-102-01-S-S-SM](#) [TMM-106-01-G-D-SM](#) [TMM-104-03-S-S](#) [TMM-102-03-G-S](#) [TMM-102-01-G-D-SM](#) [TMM-115-01-L-D](#) [TMM-104-01-L-D](#) [TMM-105-01-G-D-RA](#) [TMM-104-01-T-D-SM](#) [TMM-104-01-G-D-SM](#) [TMM-105-01-L-D-SM](#) [TMM-106-01-S-D-SM](#) [TMM-112-01-L-D](#) [TMM-105-01-T-S-SM](#) [TMM-103-02-L-D](#) [TMM-104-01-S-D-SM-P-TR](#) [TMM-105-01-S-D-SM](#) [TMM-102-01-L-D-SM](#) [TMM-102-01-G-S-SM](#) [TMM-104-06-G-D-SM-P-TR](#) [TMM-110-01-L-D-SM-A](#) [TMM-107-03-S-S](#) [TMM-103-01-S-D-RA](#) [TMM-103-01-T-D-SM](#) [TMM-105-06-G-D-SM](#) [TMM-112-01-T-D-RA](#) [TMM-110-01-L-S](#) [TMM-115-01-T-D-RA](#) [TMM-108-01-S-D-SM](#) [TMM-117-01-T-D-RA](#) [TMM-121-03-S-D](#) [TMM-122-01-L-D-SM](#) [TMM-140-01-L-D-RA](#) [TMM-115-01-L-D-SM](#) [TMM-130-01-T-D-RA](#) [TMM-120-03-T-D](#) [TMM-130-01-S-S-SM](#) [TMM-135-03-G-D](#) [TMM-140-01-G-D](#) [TMM-122-01-G-D-SM](#) [TMM-118-03-L-D](#) [TMM-122-01-T-S-RA](#) [TMM-120-06-L-D-SM](#) [TMM-122-01-S-D](#) [TMM-102-01-G-D](#) [TMM-103-01-L-S-RA-002](#) [TMM-102-01-F-S-SM](#) [TMM-102-01-TM-S-RA](#) [TMM-103-01-S-D-SM-003](#) [TMM-103-06-S-D-SM-P](#) [TMM-102-03-L-S](#) [TMM-104-01-F-D-RA](#) [TMM-104-01-T-D-RA](#) [TMM-104-03-L-S](#) [TMM-107-01-S-S-RA](#) [TMM-105-01-F-D-RA](#) [TMM-106-01-S-D-SM-P](#) [TMM-110-01-S-D](#) [TMM-111-01-T-D-RA](#) [TMM-106-01-S-D](#) [TMM-106-01-S-D-RA](#) [TMM-113-01-S-D](#) [TMM-106-06-S-D-SM](#) [TMM-109-01-L-D](#) [TMM-110-01-G-D-RA](#) [TMM-112-02-G-D](#) [TMM-113-03-L-D](#) [TMM-104-01-S-D](#) [TMM-106-01-S-S-SM](#) [TMM-113-01-T-Q-RA](#) [TMM-112-01-G-D](#) [TMM-111-01-T-S-SM](#) [TMM-112-01-G-S](#) [TMM-112-03-T-S-004](#) [TMM-107-01-G-D-SM](#)