

Smart siren



PRODUCT DATA

Built-in backup battery:	3.7 V / 350 mAh, lithium
Backup battery standby time:	About 4 hours
Consumption at alarm:	≤ 300 mA
Noise level (1 m):	High 105 dB, medium 85 dB, low 75 dB
Operational temperature range:	-10°C to 55°C
Alarm duration:	Tamper alarm 3 minutes, control alarm 1–60 minutes
Wi-Fi Frequency:	2.4 GHz
Network protocol:	IEEE802.11 b/g/n
Compatibility:	APP: DELTACO SMART HOME
Package contents:	Smart siren, USB cable, USB power adapter and manual

LOGISTICS DATA

Article number:	SH-SI01
Brand:	DELTACO
EAN code:	7333048045584
Country of origin:	China
Custom tariff number:	85182100
Master carton packing unit:	N/A
Master carton gross weight:	N/A
Master carton dimensions:	N/A
Package type:	Box
Package weight:	N/A
Package dimensions:	N/A
Article weight:	N/A
Article dimensions:	N/A

WiFi 2.4 GHz
Up to 105 db
Built-in battery backup

