

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731120214

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 20-24 AWG



Documents:	
Packaging Specification 1731120004-PK-000 (PDF)	Brochure (PDF)
Datasheet (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	D-Sub Products
Series	173112
Contact Type	Machined Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Type	Standard Density
UPC	889056489690
Physical	
Durability (mating cycles max)	200
Gender	Female
Material - Contact	Brass
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	0.200µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size AWG	20, 22, 24
Electrical	
Current - Maximum per Contact	7.5A
Material Info	
Engineering Number	FK20SL-02V-5783
Reference - Drawing Numbers	
Packaging Specification	1731120004-PK-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

173112 Series

Use With

FCT Standard-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

173112-0214