

MR1000 SERIES DETECTOR SWITCH

ANTI-VANDAL SWITCHES
 DETECTOR SWITCHES
 DIP SWITCHES
 KEYLOCK SWITCHES
 NAVIGATION SWITCHES
 PUSHBUTTON SWITCHES
 ROCKER SWITCHES
 ROTARY SWITCHES
 SLIDE SWITCHES
 SNAP ACTION SWITCHES
 TACTILE SWITCHES
 TOGGLE SWITCHES
 CAP OPTIONS




APPLICATIONS / MARKETS



Commercial Appliances



Security Devices



Vending Machines



HVAC



Industrial Controls



Medical Equipment

RoHS

SPECIFICATIONS

Contact Rating: 0.5A, 10VAC or 10VDC
Contact Resistance: 150MΩ
Contact Arrangement: SPST N.O.

FEATURES & BENEFITS

- Recessed switch
- Magnetic contact
- 9.52 [0.375 in] Press fit
- 457.20 [18.000 in] #22AWG wire leads
- Closed gap options

PART NUMBER CONFIGURATOR

Series



MR1000

DIM "X"



A - 19.0 [0.75 in]
 B - 25.0 [1.00 in]

Housing Color



W - White

Lead Length



A - 457.20 [18.000 in]

Specifications subject to change without notice 9.19.2018



E-SWITCH®



www.e-switch.com

800.867.2717

1

MR1000 SERIES DETECTOR SWITCH

BODY DIMENSIONS



| | DIM "X" | DIM "X" |
|---------------|--------------------|--------------------|
| CLOSED GAP | A = 19.0 [0.75 in] | B = 25.0 [1.00 in] |
| DEPARTURE GAP | A = 22.0 [0.87 in] | B = 28.0 [1.10 in] |

