

GSB 13 RE Professional

Combi



Specification	
Rated torque	1.8 Nm
No-load speed	0 – 2,800 rpm
Drill spindle connecting thread	1/2" – 20 UNF
Battery capacity	4,0 Ah
Chuck capacity, min./max.	1.5 / 13 mm
Impact rate at no-load speed	0 – 44,800 bpm
Max. drilling diameter in wood	25 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	15 mm
Max. drilling diameter in concrete	13 mm
Part number	0601217170

The handiest tool in its class

Key Product Features	Consumer Benefit
Extremely handy	no bigger than a glove and 1.8 kg light
Softgrip	for a secure hold
Electronic control	for exact pilot drilling
Speed preselection	with setting wheel
Robust, twin-sleeve keyless chuck	for fast bit changes
3 year tool warranty and 2 year battery warranty*	100% consumer confidence



You Tube [youtube.com/BoschProfessionalUK](https://www.youtube.com/BoschProfessionalUK)

f [facebook.com/BoschProfessionalPowerToolsUK](https://www.facebook.com/BoschProfessionalPowerToolsUK)



BOSCH
Invented for life

* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide