

AMP AMP Connect

MAIN MENU HELP
FAMILIES REGISTRATION

Alphabetical Picture Part Number
SEARCH SEARCH SEARCH

Go To Step Search™ Screen

206137-1 -- 1 of 1 products

**CPC (Circular Plastic) & Metal-Shell CPC Connectors
CPC Connectors**

General **INFO**

Sales **INFO**

Customer Drawings
SPECIFICATIONS

CAD Geometry

CPC Connectors, Series 3



Line art represents typical product only.

-  [Line Art](#)
-  [Contact Arrangement](#)
-  [Panel Cutout](#)

Searchable Features:

Product Type	Connector
# of Positions	7
Sex	Receptacle
Preloaded	No
Pin/Socket	Pin
Terminate To	Wire
Shell Size	23
Shell Type	All Plastic
Shell Thread Size	1-3/8 - 18 UNEF-2A
Numbering	Standard
Product Series	Series III
Panel Attachment	Yes
Panel Hole Type	Mounting Holes
Sealed	Yes
VDE Tested	No

Other Properties:

Dim. A	1.635 [41.53] in. [mm]
Dim. B	.520 [13.21] in. [mm]
Dim. C	.156 [3.96] in. [mm]
Dim. D	1.438 [36.53] in. [mm]
Dim. E	1.510 [38.35] in. [mm]
Dim. F	1.438 [36.53] in. [mm]
Dim. G	1.750 [44.45] in. [mm]
Dim. H	.150 [3.81] in. [mm]
Dim. J	1.610 [40.89] in. [mm]
Wire Insulation Diameter	.220 [5.59] in. [mm]
Panel Attachment Method	Square Flange
Housing Material	Thermoplastic
Housing Material Flammability Rating	UL 94V-0
Housing Color	Black