


SPE-82HQ - Loudspeaker



Hi-fi wall and ceiling speaker, 50 W, 8 Ohm

- 2-way version with coaxial dome tweeter
- 20 cm (8") bass speaker with waveguide and 25 mm (1") silk dome
- Excellent sound characteristics
- Stylish flush fit protective metal grille with slim plastic frame
- Protective grille magnetically attached to the speaker front
- For a wall thickness/ceiling thickness from 6 to 35 mm



Technical Data

Frequency range	: 30-20,000 Hz
Resonant frequency (fs)	: 40 Hz
Music power (P _{MAX})	: 100 W
Power rating (P _{RMS})	: -
Sensitivity	: 89 dB/W/m
Mounting cutout	: Ø 252 mm
Mounting depth	: 97 mm
Dimensions	: Ø 295 mm x 100 mm
Weight	: 1.8 kg