

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	38[mm]
<b>Max. Air Flow:</b>	141.2[CFM]
<b>Max. Air Flow:</b>	4[m3 per min]
<b>Max. Static Pressure:</b>	1.04[In H2O]
<b>Max. Static Pressure:</b>	260[Pa]
<b>Fan Speed:</b>	6700[RPM]
<b>Noise:</b>	61[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage - Lower:</b>	14[V]
<b>Operating Voltage - Upper:</b>	27.6[V]
<b>Current:</b>	0.92[A]
<b>Input Power:</b>	22.1[W]
<b>Mass:</b>	230[g]
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	PCN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09238RA-24P-GA-00](#)