



PANEL CUT-OUT

Rating : 15A 125V AC T105 UL cUL  
 Insert And Extract Force: 1.36kgf~6.8kgf  
 Terminal Strength: ≥80N  
 Operating Life: ≥5000 cycles  
 Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min  
 terminals to Base:3750V AC (50-60Hz)1min  
 Leakage Current : 1mA  
 Insulation Resistance: ≥100MΩ 500V DC  
 Body Materil: NYLON 66 94V-2-0

序号	部品名称	材质	处理	数量	备注
1	DB-F-M2 塑胶件	PA66	黑色	1	
2	DB-F-MS 铜件	黄铜	镀锡	2	

A4				普通公差	深圳市华灿天禄电子有限公司						
A3				COMMON TOLERANCE :							
A2				UP TO 5	±0.20	单位	mm	投影	Ac Inlet C14型	比例	Free
A1				ABOVE 5 TO 30	±0.30	UNIT		PROJECTED			
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	绘图	黄旭程	核对	品名	型号	DB-F
						DATE	2015.07.27	核准	料号	DB-F-M2	