

TORQUE WRENCH 1/2 INCH DR REV 350NM

Item ID: 1292AG-E4R



- 1/2" drive bi-directional torque wrench covering 70-350Nm
- Equipped with an in-built angular gauge for easier after tightening of stretch bolts (TTY torque to yield fasteners)
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Additional ft/lb reference scale (range 50-250 ft/lb)
- Clearly marked with three bands to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Twist locking facility to ensure the set torque is maintained
- Push through square drive for use on clockwise and anti-clockwise fastenings
- Reversible 24 teeth ratchet mechanism (DIN3122) giving 15° increments for strength and for added reference when torqueing stretch bolts
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in a handy storage case

Length (mm): 70

Width (mm): 90

Height (mm): 670

Weight (kg): 3.297

Technical changes and errors may occur

WWW.TENGOOLS.COM



Get organised™