

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Multi-Cutter

GOP 55-36 Professional

**from GBP 236.68***

* Price including VAT

Best performance for toughest applications in the Bosch StarlockMax category

The most important data

Rated input power	550 W
No-load oscillation	8.000 – 20.000 opm
Oscillation angle on left and right	1,8 °

Part number: 0 601 231 100[> More product information](#)

Technical Data

Battery and power

Rated input power	550 W
-------------------	-------

Performance data

No-load oscillation	8.000 – 20.000 opm
Oscillation angle on left and right	1,8 °

Size and weight

Weight	1,6 kg
--------	--------

Noise/vibration information

Grinding

Vibration emission value ah	3,5 m/s ²
Uncertainty K	1,5 m/s ²

Sawing with plunge-cutting saw blade

Vibration emission value ah	10,5 m/s ²
Uncertainty K	1,5 m/s ²

Sawing with segment saw blade

Vibration emission value ah	6,5 m/s ²
Uncertainty K	1,5 m/s ²

Scraping

Vibration emission value ah	6,5 m/s ²
Uncertainty K	1,5 m/s ²

Noise

Sound pressure level	81 dB(A)
Sound power level	92 dB(A)
Uncertainty K	3 dB



Product data sheet

Power tools for trade & industry

Advantages

- 550 W motor and superior Starlock interface with optimised 3-dimensional tight fit for best power transfer
- Highly durable due to robust metal components
- Snap-in function enables fast and easy tool accessory changes
- Metal cap for especially robust use
- 3D interface for low-loss power transfer from the tool to the accessory

