

# 领亚电子科技股份有限公司

No.2, The  
Fourth West Industrial Road, High-Tech Industrial Development Zone,  
Songshan Lake, Dongguan City, Guangdong Province, China  
Tel:(86)-769-85550688 Fax:(86)-769-85550388

## 承 认 书

### SPECIFICATION FOR APPROVAL

产 品: UTP CAT. 5e 4P AS

PRODUCT

料 号: \_\_\_\_\_

PART NO.

客户名称: Chipdip

CUSTOMER

承认书编号: TX-026A0603-A

SHEET NO.

客户 料号:

CUSTOMER NO.

UL/CSA STANDARD: \_\_\_\_\_

Non-standard:

日 期: 2019-5-17

DATE:

CUSTOMER CONCLUSION:  APPROVED (承认)

(客户判定)

LIMIED (允收)

REJECT (拒收)

CONDITIONAL APPROVAL (条件认可)

INCLUDING THIS COVER TOTAL 3 PAGES

(含封面页共 3 页)

\* PLEASE SIGNED AND FAX THE RESULT TO US.

(请于判定签名后将结果传回)

AUTHORIZED SIGNATURES

## 领亚电子科技股份有限公司

No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,  
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

### CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-026A0603		PART NO.	
UL FILE NO.		UL STYLE		NON-STANDARD
CSA FILE NO.		CSA STYLE		版本 A
CONSTRUCTION ITEM/ 结构项目		结构项目		
CONDUCTOR 导体	CONSTRUCTION 构造规格	AWG	7/0.160±0.008	
	MATERIAL/导体材质	-----	BARE STRAND COPPER CONDUCTOR	
INSULATION 绝缘	MATERIAL/材质	-----	HDPE	
	OD / 芯线外径	mm	0.90±0.1	
	AVERAGE THICKNESS 平均厚度	mm	0.19(REF)	
	COLOR / 颜色	-----	1P. WHITE&BROWN    2P. WHITE&BLUE 3P. WHITE&ORANGE    4P. WHITE&GREEN	
INNET-ASSEMBLE 内集合	OD/绞合外径	mm	3.8 (REF)	
INSIDE-TAPE WRAP 内部包装	MATERIAL/包带材质	-----	/	
	CONDUCTIVE/导电面	-----	/	
	OVERLAP RATE/重叠率	%	/	
DRAIN WIRE 地 线	CONSTRUCTIO/构造	mm	/	
	MATERIAL/导体材质	-----	/	
OUTSIDE-SHIELD 外部遮蔽	MATERIAL/包带材质	-----	/	
	CONDUCTIVE/导电面	mm	/	
	OVERLAP RATE/重叠率	-----	/	
JACKET 外被 MARKING 喷字	MATERIAL/材质	-----	PVC	
	DIAMETER/线径	mm	5.2±0.2	
	AVERAGE THICKNESS 平均厚度	mm	0.65(REF)	
	COLOR/颜色	-----	OPTIONAL	
	MARKING COLOR/ 喷字颜色	-----	BALCK or WHITE	
	JACKET 外被	-----		

LY-QPM-FOR-053 A/0

**领亚电子科技股份有限公司**  
 No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,  
 Songshan Lake, Dongguan City, Guangdong Province, China  
 Tel:(86)-769-85550688 Fax:(86)-769-85550388  
**CABLE SPECIFICATION(线材承认书)**

SPEC NO.	TX-026A0603		PART NO.		
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A


**Electric characters**

1.Voltage rating(额定电压)	30V
2.Temperature rating(额定温度)	75°C
3.Spark test(火花测试)	1.5KV
4.Dielectric strength(耐压强度)	AC-500V/MIN
5.Insulation resistance(绝缘电阻)	100 M OHM/KM MIN at 20°C

**Physical Characters**

- Tensile strength before aging(老化前抗张强度测试)
  - Jacket : >1.05kg/mm<sup>2</sup>
- Elongating before aging (老化前断裂伸长率)
  - Jacket : > 100%

Environmental requirements: 1. 不含双方签订的环保标准的 1 级管理物质



APPROVER		CHECK		DESIGNER	LLL
----------	--	-------	--	----------	-----