








Number of contacts

10+

16 A 250 V 4 kV 3

Han A

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han A®, Crimp termination  <p>Please order crimp contacts separately.</p>	0,14 ... 4	09 20 010 3001	09 20 010 3101	 <p>1) Distance for contact max. 24 mm</p>
Han A®, Screw termination, Contact surface: Silver plated 	0,75 ... 2,5	09 20 010 2612	09 20 010 2812	 <p>1) Distance for contact max. 24 mm                      Stripping length 7.5 mm                      Tightening torque 0.5 Nm</p>
Han A®, Screw termination, With wire protection, Contact surface: Silver plated 	0,75 ... 2,5	09 20 010 2614	09 20 010 2814	 <p>1) Distance for contact max. 24 mm                      Stripping length 7.5 mm                      Tightening torque 0.5 Nm</p> <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out for use without hood</p>