



Fuse-link, high speed, 16 A, AC 240 V, DC 150 V, BS88, 18 x 56 mm, aR, BS

Catalog No. 16LET

Delivery program

| | | | |
|------------------------------|---|----|--|
| Product range | | | Fuse |
| Basic function | | | Fuse-link |
| Field of application | | | high speed |
| Rated current | I | A | 16 |
| Rated voltage | | | AC 240 V DC 150 V |
| Construction size | | | BS88 |
| Size | | | 18 x 56 mm |
| Utilization category | | | aR |
| Breaking Capacity | | kA | 200 |
| usable for size/applications | | | protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters |
| Standard/Approval | | | BS |
| Shape | | | offset bolted tags |
| Standards/Regulations | | | BS88-4 IEC 60269-4 |
| Optional accessories | | | fuse-holder BH-0111 |

Technical data ETIM 7.0

| | | | |
|---|--|----|-------|
| Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055) | | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015]) | | | |
| Construction size | | | Other |
| Rated current | | A | 16 |
| Rated voltage | | V | 240 |
| Voltage type | | | AC/DC |
| Rated switching capacity | | kA | 200 |
| Utilization category | | | Other |
| Type of fuse status indicator | | | None |
| Insulated metal gripping lugs (IMGL) | | | No |

Additional product information (links)

| | |
|-------------------------|---|
| Product datasheet (pdf) | http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-b/Bus_Ele_DS_720004_LCT_LET_LMT_LMMT.pdf |
| Product datasheet (web) | http://www.cooperindustries.com/content/public/en/bussmann/electrical/products/high_speed_british/bs_88_240v.html |