




SIGN	DESCRIPTION	DATE	APPROVER
△	---		
△			



Technical Data:

Electrical:

- Voltage rating: 12VDC
- Current rating: 5A
- Contact resistance: 20mΩ
- Insulation resistance: 5000MΩ / 1000V
- Wire range: 22-16AWG

Mechanical:

- Torque: 0.5Nm (4.4lb/in)
- Operating temperature: -40°C to 105°C
- Strip length: 8-9mm

		Concept Design Manufacture		<small>CIE-Group Ltd 3 Widdowson Close Blenheim Ind Est Bulwell Nottingham NG6 8WB England T: +44(0)115 9770075 F: +44(0)115 9770081 E: info@cie-group.com W: www.cie-group.com</small>	
		APPROVED: RIKKI		NAME:	
TOLERANCE X ±0.50 X.X ±0.30 X.XX ±0.20 X° ±1°		CHECKED: CAMILY		2.5 Female DC Jack Quick Terminal Adapter	
DRAWN: SHERMAN		UNIT: mm	REV.: A	PART NO: CLB-JL-8114	
		SCALE: 4/1	PAGE: 1/1	DWG NO.:	