



■ SPECIFICATIONS


- Voltage rating: 250V AC, DC
- Current rating: 5A, AC, DC
- Withstanding Voltage: 1500V AC/minute
- Temperature range: -25° C~+85° C
- Contact resistance: 20mΩ max

■ TERMINAL


- Applicable wire: AWG#22-#26
- Material: Brass
- Finish: Tin Plated
- The Dimension Marked "▼" Must Be Recorded



SECTION: A-A



SECTION: B-B



SECTION: C-C

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司		SHEET	1/1	
				X.	±0.30	X°	±5°	CONNECTORS XFCN CONNECTORS CO., LTD.		DATE	2010. 4. 12	
				.X	±0.20	.X°	±2°	PRODUCT NAME	2.54mm Crimp Style Connectors		UNITS	mm
				.XX	±0.08	.XX°	±1°	PART. NO.	T2553BS-2		SCALE	1:1
AO	MODIFICATION		DRAW	DATE	.XXX	±0.03	.XXX°	VIEW			DWG NO.	009