

"MINI" AUTOMOTIVE FUSE CLIPS & HOLDERS


For .110 (2.8) × .032 (.80) MINI BLADE FUSES
 For Littelfuse Mini 297 or 997 series/Bussmann ATM series or equivalent

VERTICAL FUSE ENTRY

Thru Hole Mount



- Low Profile



CAT. NO. 3564

MATERIAL:


.016 (.41) Brass, Matte Tin Plate
Current Rating: 15 Amps @ 500V AC

AVAILABLE ON TAPE AND REEL

Surface Mount



- Low Profile




CAT. NO. 3563 (Bulk)


CAT. NO. 3563TR (Tape & Reel)

Tape & Reel Spec's: 24mm wide; 12mm pitch; 13 inch reel (1500 pieces per reel)

Mounting Detail For Two Clips




Pad Layout For Two Clips





SPECIFICATIONS

Material: .012 (.30) Brass
Insulator: Glass filled Nylon, UL Rated 94V-0
Current Rating: 15 Amps @ 500V AC
Temperature Rating: -58°F to +292°F (-50°C to +145°C)



CAT. NO. 3544 Tin-Nickel Plate

Mounting Detail For Two Clips



CAT. NO. 3544-2 Tin Plate


LOW PROFILE MINI FUSE HOLDER

For Littelfuse Low Profile Mini 897 series or equivalent

- Low insertion force
- Thru hole PC mountable, maintains position during wave soldering
- Fuse holder fully insulates clips to protect fuse from shorting
- Holder assures proper spacing and reduces assembly time


SPECIFICATIONS

Contacts: .016 (.41) Brass, Tin-Nickel Plate
Insulator: Nylon 4/6, UL Rated 94V-0
Current Rating: 20 Amps @ 500V AC
Temperature Rating: -58°F to +292°F (-50°C to +145°C)




CAT. NO. 3557-2

Mounting Detail



Refer to page 39 for Cat. No. 3557 Clip details

Mounting Detail




MINI FUSE HOLDER

For Littelfuse Mini 297 or 997 series/Bussmann ATM or equivalents

SPECIFICATIONS

Contacts: .016 (.41) Brass, Tin-Nickel Plate
Insulator: Nylon 4/6, UL Rated 94V-0
Current Rating: 20 Amps @ 500V AC
Temperature Rating: -58°F to +292°F (-50°C to +145°C)




CAT. NO. 3568

HORIZONTAL FUSE ENTRY

For Littelfuse Mini 297 or 997 series/Bussmann ATM series or equivalent



SPECIFICATIONS

Contacts: .012 (.30) Brass
Insulator: Nylon 6/6, UL Rated 94V-0
Current Rating: 15 Amps @ 500V AC
Temperature Rating: -58°F to +292°F (-50°C to +145°C)



CAT. NO. 3549 Nickel Plate

Mounting Detail For Two Clips



CAT. NO. 3549-2 Tin Plate



"AUTO" FUSE CLIPS & HOLDERS