

CT2988

2 mm Digital Multimeter Probes

Datasheet

Pair, black & red, standard size probe bodies w/2mm pintips

Description

Black and red pair of standard size probe bodies with 2 mm (.080) x 19 mm (0.75) pintips.

Bodies accept 4 mm sheath (safety) banana plug test leads.

Features:

- Standard size bodies: 96 mm (3.8") length
- Tips: Brass, Nickel Plated
- Tip fits into North American power sockets

Individual colors available as Model CT2266.

Warning: An exposed tip length greater than 4 mm limits the probes to CAT II measurement categories.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Cal Test
ELECTRONICS 

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

| | |
|------------------------------|----------------|
| IEC Rating | 1,000 V CAT II |
| Current Max | 36 A |
| Temperature (degrees) | -20 to +80C |
| RoHS (2011/65/EU) | Compliant |

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2988](#)