



SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C



Contact Material: Brass
 Contact Plating: Au Or Tin Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Ordering Information

1225 11 XX X N XX R XXX X 01

No. of Pins Per Row: 1x40, 1--40
 Insulator Material Option:
 A=BK-PBT, B=BK-PA66, C=BK-PA6T, D=BK-PA46, F=BK-LCP
 Contact Plating:
 G0:0.8U" Gold, G1:1.0U" Gold, G2:1.5U" Gold, G3:2U" Gold, G4:3U" Gold
 SN: Tin
 Pin Length:
 Packing:
 O=PE Bag, A=Tray, T=Tube, P=Tube+Cap, R=Reel+Cap, M=Reel+Mylar



Dimension orntitheses list				
ITEM	PA	PC	PB	L
Standard	6.00	3.00	4.40	13.80
Alternate				

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	WZG	14.08.08	SCALE		FIT	SHEET	PROJ.	TITLE:
				Angle	DIM				UNIT	SIZE				
A0	2012.07.02	NEW DRAWING		X.X	±3°				mm	A4	1/1			2.54mm Pin Header 2.5mm Single 90°正弯

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

PART NO. 122511XXXXRXXXX01