







Cixi Dibo Electronics Co., LTD

产品规格书
product specification



P.C.B. LAYOUT




TOLERANCES EXCEPT AS NOTED

linear dimension (Tolerances Standard GB/T 14486-2009)

tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4
variable range	6 to	6 to	10 to	18 to	30 to	50 to	80 to	120 to	160 to	200 to	250 to	all	5 to	5 to	30 to	120 to
over	6	10	18	30	50	80	120	160	200	250			5	30	120	

订购方式： HOW TO ORDER



电气性能/Electrical
 参考标准/Standard: UL IEC
 额定电压/Rated voltage: 300V 250V
 额定电流/Rated current: 8A 15A
 接触电阻/Contact resistance: 20m Ω
 使用线径/Wire range: 26-14AWG 1.5mm²
 耐电压/Withstanding voltage: AC2000V/1Min
 绝缘电阻/Insulation resistance: 500M Ω /DC/500V

机械性能/Mechanical

温度范围/Temp Range: -40°C+105°C
 扭矩/Torque: 0.4Nm(3.5lb`in)
 剥线长度/Strip length: 6-7mm

尺寸/Dimensions

间距/Pitch: 5.0mm
 极数/Poles: 2P-24P

材料及电镀/Material

塑件/Housing: PA66, UL94V-0
 螺丝/Screws: M2.5, steel Zinc plated
 方针/Pin header: Brass, Ni plated
 弹片/Shrapnel: Phosphor bronze, Ni plated

Cixi Dibo Electronics Co., LTD

名称/NAME

DB126V-5.0

第一视角/THIRD ANGLE PROJECTION

