


## prevoS1 blow gun with OSHA metal nozzle



### Technical characteristics

**Profile:**

**Max operating pressure:** 12 bar


**Temperature:** -15°C to +70°C

**Construction:** Polyamide composite body

**Highlight:** Compact

**Connection:** Built-in adaptor

prevoS1 coupler sold separately: ASI 06

	A (mm)	B (mm)	Blowing force (at 6 bar (g))	Dynamic pressure (at 10 mm at 6 bar (bar))	Air consumption (at 6 bar (Nm <sup>3</sup> /h))	Sound level (at 6 bar (dB(A)))	Parts Numbers
	179	97	248	2.3	13	89	<b>ABG 06MTLH</b>