



## Luminaire Connectors and Block Connectors

### ZEL 900 - Strain relief clamp for luminaire connectors



#### Technical data

**Connection** cables Ø 5.0 - 12.0 mm  
 releasable by pressing the catch springs to the side

**Fixing** to connector and/or screw M4

**Moldings** polycarbonate white  
 flammability rating to UL 94: V-0  
 continuous working temperature 125 °C  
 short-time temperature 165 °C

#### Upon request

strain relief with catch pins (ZEL 980); further product variants [here](#)

#### For use with

LK 980/ 3	3 pole luminaire connectors
LK 980 RZ/ 3	3 pole luminaire connectors, with catch pins
LK 980/ 4	4 pole luminaire connectors
LK 980 RZ/ 4	4 pole luminaire connectors with catch pins
LK 980/ 5	5 pole luminaire connectors
LK 980 RZ/ 5	5 pole luminaire connectors, with catch pins

#### Order info

Description	Item	Order No.	PU	
Fixing by screw	ZEL 900	196423	500	> ☞

