
Field-Attachable Connectors BCC M478-0000-1A-000-43X834-000 Order Code: BCC04MC






EHE 🕱

Basic features		Environmental conditions	
Approval/Conformity	EAC WEEE	Ambient temperature IP rating	-2585 °C IP67
Electrical connection		Material	
Cable diameter D	48 mm	Material contact carrier	PA
Connection	M12x1-Female, Straight, 8-pin, A-	Material contacts	Bronze
	coded	Material cover nut	Die-cast zinc
Contact shield	Iris spring		nickel-plated
Number of connectable contacts	8	Material grip	Die-cast zinc
System	Can be fabricated		
		Mechanical data	
Electrical data		Connection cross-section	0.140.34 mm ²
Operating voltage Ub	30 VDC / 30 VAC	Type of wire mounting	IDC
Rated current (40 °C)	1.75 A		

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



Internet