




Every part matters

EN

Datasheet

RS PRO IN-LINE 4 WAY 17MM CONNECTOR 5A IP68 (SHELL ONLY)

Stock Number: 181-1439





Material and Specification

| | |
|----------------------------|--|
| Material | Plastic |
| IP Rating | IP68 |
| Coupling Type | Threaded coupling |
| Shell | Nylon66, fire resistance:V-0 |
| Insert material | PPS max temperature 260°C, fire resistance:V-0 |
| Contact material | Brass with gold plating |
| Termination | Solder/Crimp |
| Cable outer diameter range | 6-10mm |
| Mating cycle | > 500 |
| Temperature range | -25°C~+85°C |
| Insulation resistance MΩ | 2000 |