




Every part matters

EN

Datasheet

RS PRO CABLE MOUNT 2 WAY 17MM CONNECTOR 10A IP68 (SHELL ONLY)

Stock Number: 181-1440





Every part matters

EN

Material and Specification

Material	Plastic
IP Rating	IP68
Coupling Type	Threaded coupling
Shell	Nylon66, fire resistance:V-0
Insert material	PPS max temperature 260°C, fire resistance:V-0
Contact material	Brass with gold plating
Termination	Solder/Crimp
Cable outer diameter range	6-10mm
Mating cycle	> 500
Temperature range	-25°C~+85°C
Insulation resistance MΩ	2000