

| REV. | DESCRIPTION    | DRAWN        | CHECKED | APPROVED     |
|------|----------------|--------------|---------|--------------|
| A    | NEW RELEASE    | LJC 01/16/09 | ~~~~    | LJC 01/16/09 |
| H    | DRAWING UPDATE | JLZ 05/20/17 | ~~~~    |              |




TOLERANCE:

| Abbr. | TOLERANCE  |             |              |               |        |        |        |
|-------|------------|-------------|--------------|---------------|--------|--------|--------|
|       | P=0.50     | P=0.80      | P=1.00       | P=1.25        | P=1.50 | P=2.00 | P=2.54 |
| P     | ±0.050     | ±0.080      | ±0.080       | ±0.100        | ±0.125 | ±0.150 | ±0.250 |
| Pt    | ±0.050     | ±0.080      | ±0.080       | ±0.100        | ±0.125 | ±0.150 | ±0.250 |
| W     | ±0.050     | ±0.080      | ±0.080       | ±0.100        | ±0.125 | ±0.150 | ±0.250 |
| M     | ±0.050     | ±0.080      | ±0.080       | ±0.100        | ±0.125 | ±0.150 | ±0.250 |
| Cw    | ±0.020     | ±0.030      | ±0.030       | ±0.030        | ±0.030 | ±0.040 | ±0.040 |
| L     | (15~100)±3 | (101~300)±5 | (301~600)±10 | (601~1000)±15 |        |        |        |

NOTES:

- Insulation material: PVC  
Supporting Tape material: Polyester  
Conductor material: Tin plated copper
- Product Number Code  
DS1057-03 - X X X X X X X X X X

- Cable Style  
A: A type  
B: B type
- Cable Thickness  
1: 0.12mm
- Total Length(Dim L)  
A: 110mm  
B: 150mm  
C: 120mm ⑧  
D: 160mm ⑧  
E: 100mm ⑧  
F: 200mm ⑧  
G: 250mm ⑧
- Supporting tape Length  
4: 4.0mm 5: 5.0mm  
6: 6.0mm 8: 8.0mm  
10: 10.0mm
- Supporting Tape color  
L: Blue
- Strip Length  
2: 2.0mm 3: 3.0mm  
4: 4.0mm 5: 5.0mm  
6: 6.0mm
- Insulation color  
W: White
- No.Of positions  
02: 2pin  
⋮  
60: 60pin
- Conductor Size  
H: 0.035x0.65mm(Ph 1.0mm)  
J: 0.035x0.3mm(Ph 0.5mm)  
K: 0.05x0.8mm(Ph 1.25mm)
- Pitch  
1: 1.00 5: 0.50  
2: 2.00 6: 1.25  
3: 1.50 8: 0.80  
4: 2.54



|           |       |
|-----------|-------|
| Ft1±0.005 | 0.043 |
| Ft2±0.005 | 0.043 |

| Pitch  | No.Of positions | Conductor Size<br>Ct*Cw (mm) | Strip Length<br>S1=S2 (mm) | Supporting tape Length<br>D1=D2 (mm) |
|--------|-----------------|------------------------------|----------------------------|--------------------------------------|
| p=0.50 | 06~60pin        | 0.035x0.3                    | 3or4                       | 6or8                                 |
| p=0.80 | 06~40pin        | 0.05x0.5                     | 4or5                       | 8or10                                |
| p=1.00 | 03~50pin        | 0.035x0.65                   | 4or5                       | 8or10                                |
| p=1.25 | 03~36pin        | 0.05x0.8                     | 4or5or6                    | 10                                   |
| p=1.50 | 02~30pin        | 0.10x0.5                     | 4or5or6                    | 10                                   |
| p=2.00 | 02~30pin        | 0.10x0.5                     | 3or4or5or6                 | 5or6or8or10                          |
| p=2.54 | 02~18pin        | 0.10x0.7                     | 4or5or6                    | 10                                   |
|        |                 | 0.10x1.27                    |                            |                                      |

| GENERAL TOLERANCE |       | ANGLE TOLERANCE |     |
|-------------------|-------|-----------------|-----|
| X.                | ±0.60 | X.              | ±5° |
| .X                | ±0.38 | .X              | ±3° |
| .XX               | ±0.25 | .XX             | ±2° |

|            |    |            |                             |
|------------|----|------------|-----------------------------|
| PROJECTION |    | TITLE      | UL 20624 FLEXIBLEFLAT CABIE |
| UNITS      | mm | SHEET SIZE | A4                          |
| SHEET SIZE | A4 | SERIES     | DS1057-03                   |

|              |                          |
|--------------|--------------------------|
| DRAWING TYPE | CUSTOMER                 |
| SCALE        | 1:1 SHEET 1 OF 1         |
| DRAWING NO.  | C-DS1057-03-XXXXXXXXXX-H |

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD