
MALE END VIEW
7 6 5 5 1 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6
euro Tast,

SPECIFICATIONS							
HOUSING MATERIAL/COLOR	NYLON/BLACK						
CONTACT MATERIAL/PLATING	BRASS/GOLD						
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL						
RATED CURRENT [A]	2.0 A						
RATED VOLTAGE [V]	60 VAC/75 VDC						
MAXIMUM WIRE SIZE	18 AWG						
CABLE GRIP RANGE	6-8mm						
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)						
PROTECTION CLASS	IEC IP67						
WIRE TERMINATION	SCREW TERMINALS						



## SOURCE DRAWING - FOR REFERENCE ONLY

Source Drawing - For her energy											/NL I
					RELATED DOCUMENTS  1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	Wigh Technolog	RCK Inc '	3000 CAMPUS E MINNEAPOLIS, MN 1-800-544-7' (763) 553-73 (763) 553-07 turck.com	55441 7769 300 708 fax
					SEE SPECIFICATIONS	DISPLAYED ON THIS DRAWING ARE FOR	DRFT JBJ DATE 02/27/03 APVD SCALE 1=1.0 UNIT OF MEASUREMENT MILLIMETERS		DESCRIPTION BS 8181	-0	
F	UPDATE SPECIFICATIONS	l RNS	04/04/14	45380	FINISH	CONTACT TURCK FOR MORE			IDENTIFICATION NO. U0885-25		REV E
	DESCRIPTION	BY	DATE	ECO NO.	SEE SPECIFICATIONS	INFORMATION	DO NOT SCALE	THIS DRAWING	FILE: U0885-25	SHEET	1 OF