

RJ45 overmolded patch cable Cat 6 1,0m



Image is for illustration purposes only.
Please refer to product description.

Part number:	09 47 474 7109
Description:	RJ45 overmolded pat Cat 6 1,0m
RoHS conformity:	Yes
Limiting temperature (flexible), min.:	0 °C
Limiting temperature (flexible), max.:	60 °C
Limiting temperature, min.:	-20 °C
Limiting temperature, max.:	80 °C
Degree of protection acc. to DIN EN 60 529:	IP 20
Cable length:	1 m
Material, cable:	SF/UTP, PUR