



-For solid and stranded conductors
 AWG 27 up to AWG 22
 -Max. wire diameter 1.5mm
 -Cable diameter 6 - 12mm
 -Degree of protection IP65/IP67
 -Cat. 6 performance class EA
 suitable for 1/10 Gigabit Ethernet
 -Temperature range -40°C up to +70°C
 -750 mating cycles

Data contact plating: Au 1.27µm (50µ") over nickel

			Dot.	Name	<p>All Dim. in mm Orig. Size DIN A 4</p>	Maßstab/ Scale 1,5:1
		Detail.	03/05/10	AB		
		Insp.				
		Stand.				
36074	03/05/10	AB	HARTING EURL F-95972 Paris			TB 09 45 115 1760 Sub.
Mod.	Dot.	Name				