






## Phosphated adjustable wrench

- Wide handle for comfort in use
- Improved access in confined spaces with the slim 15° angled jaws
- Accurate jaw movement
- Ultimate strength through precision hardening and high performance alloy steel
- IP = Industrial pack

### MORE DETAILS ABOUT PRODUCT

- Standards: ISO 6787, DIN 3117 form, ASME B107.8M - 1996 and BS 6333
- High performance alloy steel
- Scale in mm for pre-adjusting and accurate measurement
- Head combines slimness for accessibility with strength for performance
- Left turning screw
- Black finish. Precision-hardened and anti-corrosion treated
- IP: Industrial pack

### PRODUCT TABLE

Product	A	B	C	D	 g		
8069	110 mm	13 mm	4 mm	9 mm	60 g	13 mm	110 mm
8070	155 mm	20 mm	4.9 mm	11.3 mm	135 g	20 mm	155 mm
8071	205 mm	27 mm	6 mm	12.9 mm	255 g	27 mm	205 mm
8072	255 mm	30 mm	8.6 mm	15.5 mm	400 g	30 mm	255 mm
8073	305 mm	34 mm	11.9 mm	18 mm	665 g	34 mm	305 mm
8074	380 mm	44 mm	14 mm	20 mm	1035 g	44 mm	380 mm