

# KERN CKE3600-2

Selbsterklärende Zählwaage mit Laborgenauigkeit, Zählauflösung bis zu 360.000 Punkte



## Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

## Service

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	360 x 230 x 180 mm
Gross weight:	2,200 kg
Net weight:	1,800 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	150 x 170 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	50 mg
Readout [d]:	10 mg
Recommended adjusting weight:	2 kg (F1); 1 kg (F1)
Reproducibility:	10 mg
Resolution:	360000
Stabilisation time:	3 s
Tare range:	3,600 kg
Warm up time:	2 h
Weighing range [Max]:	3,600 kg
Weighing system:	Strain gauge
Weighing units:	g

## Display

Display digit height:	9 mm
-----------------------	------

## Counting

Counting resolution:	360000
Minimum piece weight at piece counting (Laboratory):	10 mg
Minimum piece weight at piece counting (Normal):	100 mg

## Functions

Counting function:	yes
Suspended weighing:	Hook

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C