


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0530470310](#)  
**Status:** **Active**  
**Overview:** [PicoBlade Connector System](#)  
**Description:** 1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Tin Plating, Friction Lock, 3 Circuits, Tray, 2.30mm PC Tail Length

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51021-010-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Application Specification 510210000-AS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification SPK-53047-001-001 (PDF)</a>
<a href="#">Product Specification 510211010-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

UL E29179

**General**

Product Family	PCB Headers
Series	<a href="#">53047</a>
Application	Signal, Wire-to-Board
Current Derating Order No	987651-3691
Overview	<a href="#">PicoBlade Connector System</a>
Product Name	PicoBlade
UPC	800753566231

**Physical**

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	5.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	75.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[53047](#) Series

**Mates With**

PicoBlade Housing [51021](#) <br>PicoBlade  
Cable Assembly [15134](#)

**Electrical**

Current - Maximum per Contact

1.0A

Voltage - Maximum

125V

**Material Info****Reference - Drawing Numbers**

Application Specification

510210000-AS-000

Packaging Specification

SPK-53047-001-001

Product Specification

510211010-PS-000, PS-51021-010-001

Sales Drawing

530470000-SD-000

This document was generated on 08/10/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**