

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1054500101](#)
Status: **Active**
Overview: USB Products and Solutions
Description: Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Top Mount, Surface Mount, Gold (Au) Flash over 0.76µm Palladium Nickel Plating

Documents:

[3D Model](#) [Datasheet \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General


Product Family	I/O Connectors
Series	105450
Application	Wire-to-Board
Comments	Nickel underplating
Component Type	Receptacle
Overview	USB Products and Solutions
Product Name	USB 3.1
Type	C
UPC	889056497121

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	0.539/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.70mm, 0.80mm
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.051µm (Au), 0.762µm (PdNi)
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-30° to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.25A, 1.25A, 5.0A, See Product Specification
Grounding to Panel	None
Shield Type	Full Shield



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
Perfluorohexane-1-
sulphonic acid and its
salts
Tris(4-nonylphenyl,
branched and linear)
phosphi
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
1,2-
benzenedicarboxylic
acid, dipentylester,
bra
Terphenyl,
hydrogenated
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
ammoniumpentadecafluorooctanoate
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
dibutyltin dichloride
1,2-diethoxyethane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
decamethylcyclopentasiloxane
dodecamethylcyclohexasiloxane

China RoHS

Shielded
Voltage - Maximum

Yes
30V AC/DC

Material Info

benzo[ghi]perylene
ethylene thiourea
phenanthrene
[phthalato(2-)]dioxotrilead
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Sulfurous acid, lead
salt, dibasic
cadmium hydroxide
pyrochlore, antimony
lead yellow
orange lead
1,2-bis(2-
methoxyethoxy)ethane
1,2-dimethoxyethane
bis(2-methoxyethyl)
phthalate
pentazinc chromate
octahydroxide
tetraboron disodium
heptaoxide, hydrate
tris(2-chloroethyl)
phosphate

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[105450 Series](#)

Mates With

USB Type C Plug/Cable

This document was generated on 10/23/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION