

Terminals**Part Number: 1706060000****ZDU 2.5-2/4AN****Feed-through terminal 2.5 mm²**

Representative Photo

Selected Features

Installation advice	TS 35
Type of connection	Tension spring connection
Insulation material	Wemid
Rated voltage	800 V
Rated current	24 A
Rated cross-section	2.5 mm ²
Version	Feed-through terminal
Colour of insulating material	dark beige
Current for max. conductor	24 A
Rated impuls voltage	8 kV

Additional Technical Data

EAN	4008190915407
Width	5 mm
Length	50.5 mm
No. of identical terminals	1
Voltage UL	600 V
Voltage CSA	600 V
Current CSA	23 A
Plug gauge	A2
min. conductor	0.13 mm ²
max. conductor	2.5 mm ²
Height with TS	43 mm
Degree of soiling	3
Strom UL	20 A
min. rated cross-section (UL)	26 AWG
max. rated cross-section (UL)	12 AWG
min. rated cross-section (CSA)	26 AWG
max. rated cross-section (CSA)	14 AWG
Type of Cross-connection 1	ZQB
No. of identical Cross-connection 1	1
QV 1 - Cont. current >2 pin (A)	24 A
Type of Cross-connection 2	ZQW
No. of identical Cross-connection 2	1
QV 2 - Cont. current 2 pin (A)	24 A
QV 2 - Cont. current >2 pin (A)	24 A
Stripping length	10 mm

Solid, min.	0.5 mm ²
Solid, max.	2.5 mm ²
Stranded, min.	0.5 mm ²
	2.5 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	2.5 mm ²
Flexible and ferrule, min. (DIN 46228-1)	0.5 mm ²
Flexible and ferrule, max. (DIN 46228-1)	1.5 mm ²
ferrule with plastic insul. collar, min.	0.5 mm ²
ferrule with plastic insul. collar, max.	1.5 mm ²

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America
 United States 001 (800) 849-9343
 Canada 001 (800) 268-4080

or

Weidmüller - Germany
 Telephone operator 0049 (-5252) 960-0

