

M12-PCB-SMT-2PC-5P-ACOD-M-STR(75)

	Part number	21 03 311 1516
	Specification	M12-PCB-SMT-2PC-5P-ACOD-M- STR(75)
	HARTING eCatalogue	https://b2b.harting.com/21033111516

Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

Version

Termination method	Reflow soldering termination (SMT)
Gender	Male
Shielding	Unshielded
Number of contacts	5
Coding	A-coding
Pack contents	Tape & reel

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	> 10 ⁸ Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 +85 °C
Mating cycles	≥100
Overvoltage category	III



Technical characteristics

Isolation group I (600 ≤ CTI)

Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications IEC	61076-2-101
--------------------	-------------

Commercial data

Packaging size	1
Net weight	742 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector