




ENGLISH

## M12 Connectivity

M12, 5 pole, 0°, male self wire connector

Stock No. 174-7864




### Primary Features

Knurled and hexagonal combination nut ensures secure connection


Wide cable sealing range – 2.5 mm to 8.0 mm

Wide termination range - 0.14 to 1.5 mm<sup>2</sup>

IP67 when inserted and tightened



Male





## Technical Data

174-7864

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...1.5 mm <sup>2</sup>
Sealing range (cable Ø)	2.5...8.0 mm
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)
Temperature range	-30...+85 °C
Dimensions H × W × D	61×20×20 mm