



ENGLISH

## Datasheet

### Stock No.184-5596

### RS PRO Capacitive Sensor



#### Specifications:

Mounting: Flush  
Rated distance Sn: 5mm(adjustable)  
Assured distance Sa: 0...4mm  
Shape size:M18\*70mm  
Output way: PNP  
Output status: NO+NC  
Supply voltage: 10...30 VDC  
Standard target: Fe18\*18\*1t  
Switch point offset[%/Sr]:  $\leq \pm 20\%$   
Hysteresis range [%/Sr]: 3...20%  
Repeated error:  $\leq 3\%$   
Load current:  $\leq 200\text{mA}$   
Residual voltage:  $\leq 2.5\text{V}$   
Current consumption:  $\leq 15\text{mA}$   
Protection circuit: Short-circuit, overload and Reverse polarity  
Output indicator: Yellow LED  
Ambient temperature:  $-25^{\circ}\text{C} \dots 70^{\circ}\text{C}$   
Ambient humidity: 35-95%RH  
Switch frequency: 50 Hz  
High pressure resistance: 1000V/AC 50/60Hz 60s  
Insulation resistance:  $\geq 50\text{M}\Omega(500\text{VDC})$   
Vibration resistance: Complex amplitude 1.5mm 10...50Hz(2H per X,Y,Z direction)  
Protection degree: IP67  
Housing material: Nickel-copper alloy  
Connection:2m PVC cable

#### Features:

- ◆ Be able to detect both metal and nonmetal objects;
- ◆ Be able to detect various media via nonmetallic container;
- ◆ Reliable liquid level detecting;

25/03/2019