

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



**Firestop® Technical Datasheet** 

**tasker® C128 CPR – 2x0,35 mm<sup>2</sup>**



**Low Capacity Balanced Microphone Cable – CPR Eca Class**



**CATEGORY** Balanced Microphone Cable (See Audio Catalogue)  
**APPLICATIONS** Audio and Microphone on Fix Installation

- A:** Black Flame Retardant PVC Sheath.  
Outer cable Diam. Ø 6,10 (±0,20) mm.
- B:** Braided Shielding O.F.C. tinned copper covering 85%.
- C:** The cores are stranded in a pair with two Flame Retardant PVC filler.  
Cores insulation in Flame Retardant PVC, colored one red and one white.
- D:** Diam. Ø 1,70 (±0,20) mm.
- E:** One conductor in O.F.C. red copper and one in O.F.C. tinned copper.  
formation 11x0,20 mm. Nom. Cross section 2x0,35 mm<sup>2</sup>.

**MARKING** **tasker® C128 CPR 2x0,35 mm<sup>2</sup> - IMQ 0051-CPR-0753 – 2017 – Eca – O.F.C. – Audio Cable For Fix Installation – FirestoP® - Made In Italy**

**Cable Properties**

<b>Conductor Resistance</b>	58 Ω/Km
<b>Capacity Core/Core</b>	55 pF/m
<b>Capacity Core/Shield</b>	92 pF/m
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-20/+70°C

<b>USE</b>	X	Indoor	Interno Edificio	<b>INSTALLATION</b>	X	Fixed	Fissa	<b>INFORMATION</b>	X	RoHS3 Compliant
<b>Impiego</b>	X	Outdoor Limited	Esterno Limitato	<b>Posa</b>		Restricted Mobile	Mobile Limitata	<b>Informazioni</b>	X	Ver. B / 07.06.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			