


# Power Supplies

#[SW25 Reg.]



### General characteristics

Brand: Alpha Elettronica  
 Technology: switching  
 Construction: plugin

### Electrical characteristics

Regulation type: CV  
 Output regulation: manual switch  
 Input voltage tolerance:  $\pm 10\%$   
 Frequency: 50Hz  
 Insulation class: II  
 Efficiency: 70%  
 Power: 24W  
 Output voltage tolerance:  $\pm 5\%$   
 Ripple:  $< 60\text{mV}$   
 Protections: sovraccarico, sovratempera-  
 tura, corto circuito

### Mechanical characteristics

Dimensions (LxVxH): 80mm x 34mm  
 x 59mm  
 Cooling: passive  
 Connections: interchangeable con-  
 nector  
 Connectors:

### Thermal characteristics

Working temperature:  $-10/30^{\circ}\text{C}$



Articolo	Input voltage	Output voltage	Output current	Power	Codice EAN
	230V	3V	3000mA	24W	8 017443 564398
	230V	4.5V	3000mA		
<b>SW25-40050</b>	230V	6V	2800mA		
	230V	7.5V	2500mA		
	230V	9V	2300mA		
	230V	12V	2000mA		

Confezione: Scatola da 1 pz., Imballo: Scatola da 25 scatole  
 Prezzo per: unità  
 Multiplo di vendita: 1 pz.

### Connectors

