

BACKSHELL KIT INCLUDES:

(2) BACKSHELL HALVES

(2) 4-40 THUMBSCREWS

(2) HOUSING SCREWS

(1) SET OF COMPRESSION INSERTS - (9 POSITION ~ 37 POSITION)

DIAMETERS: 4mm (.157"), 5mm (.197"), 7mm (.276"), 9mm (.351")



(1) SET OF COMPRESSION INSERTS - (50 POSITION)

DIAMETERS: 11mm (.433"), 12.5mm (.492"), 14mm (.551"), 15mm (.591")

NOTE: 9 POSITION HAS ONLY 1 THUMBSCREW

(OPPOSITE CABLE ENTRY)

DIMENSIONS (mm/in)					
SIZE:	A $\pm .25$ $\pm .010$	B $\pm .13$ $\pm .005$	C $\pm .25$ $\pm .010$	D $\pm .25$ $\pm .010$	E
9	31.00	24.99	36.30	14.50	13.00
	1.220	0.984	1.429	0.571	0.512
15	39.50	33.32	40.30	14.50	13.00
	1.555	1.312	1.587	0.571	0.512
25	53.20	47.04	40.30	14.50	13.00
	2.094	1.852	1.587	0.571	0.512
37	69.70	63.50	40.30	14.50	13.00
	2.744	2.500	1.587	0.571	0.512
50	67.40	61.11	44.90	17.40	17.00
	2.654	2.406	1.768	0.689	0.669



ORDERING INFORMATION

SIZE:	P/N KITTED:	PRODUCT CODE:
9-WAY	6560-0116-11	MHD45ZK-9-BK-K
15-WAY	6560-0116-12	MHD45ZK-15-BK-K
25-WAY	6560-0116-13	MHD45ZK-25-BK-K
37-WAY	6560-0116-14	MHD45ZK-37-BK-K

SIZE:	P/N BULK:	PRODUCT CODE:
9-WAY	6561-0116-11	MHD45ZK-9-BK
15-WAY	6561-0116-12	MHD45ZK-15-BK
25-WAY	6561-0116-13	MHD45ZK-25-BK
37-WAY	6561-0116-14	MHD45ZK-37-BK

PLASTIC: DIE CAST ZINC ALLOY

PLATING: BLACK OXIDE

4-40 THUMBSCREWS: STEEL - BLACK OXIDE PLATED

HOOD SCREWS: STEEL - BLACK OXIDE PLATED

COMPRESSION INSERTS: ABS UL RECOGNIZED

OPERATING TEMP: -40°C TO +120°C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN	DATE
P. JENKINS	03-14-12

APPROVED	DATE
D. CROFT	03-14-12

SCALE	SHEET	OF	REV:
NTS	1	1	A

DRAWING No
MHD45ZK-BK SERIES

RoHS COMPLIANT



MH CONNECTORS LTD.