

AC FAN

JAMICON®

80X80X38 mm

JA0838-0N Series



- **Motor** : Two-pole shaded pole induction motor
- **Frame** : Aluminum Alloy, Painted black
- **Impeller** : Retardant thermoplastic in black color, rated UL94V-0
- **Speed Range** : ±10%
- **Impedance protected**

SPECIFICATIONS

Model	Bearing	Nominal Voltage (V)	Frequency (Hz)	Air Flow (CFM)	Static Pressure (inchH ₂ O)	Speed (R.P.M.)	Nominal Current (Amp)	Input Power (Watt)	Noise (dBA)	Weight (g)
JA0838H1B0N	Dual Ball	110 - 120	50	21.42	0.102	2400	0.17	13	25.2	285
			60	26.46	0.149	2800		10	32.1	
JA0838H1S0N	Sleeve	220 - 240	50	20.78	0.098	2200	0.08	13	24.4	
			60	25.19	0.134	2600		10	30.0	
JA0838H2B0N	Dual Ball	220 - 240	50	22.25	0.109	2400	0.08	12	26.3	
			60	26.74	0.152	2800		9	31.9	
JA0838H2S0N	Sleeve		50	20.44	0.094	2200		12	24.2	
			60	24.19	0.122	2500		9	28.2	

Specifications subject to change without notice

