



NOTE:

- 1.Rating: 24V 25mA AC
- 2.Insulation Resistance:≥100 MΩ
- 3.Withstand voltage:AC 500V 1Minute
- 4.Operating Force Range: 800gf Max
- 5.Mechanical Life:3,000 Cycles
- 6.Operating Temperature range -20°~+70°C
- 7.Ambient Humidity used: ≤85%RH

Position(位数)	2P	4P	6P	8P	10P	
DIM.A(长度)	4.07	6.61	9.15	11.69	14.23	
DIM.B(长度)	1.27	3.81	6.35	8.89	11.43	
PART NO. 盖子/黑色(K)	短柄(S)	EP-02KS	EP-04KS	EP-06KS	EP-08KS	EP-10KS

⑤	Contact Spring	—		Phosphor bronze	Au Plating	—
④	Terminal	—		Phosphor bronze	Au Plating	—
③	Base	—	1	PBT	Black	—
②	Cover	—	1	PBT	Black	—
①	Keystoke	—		PBT	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	HRO 翰泰® ELECTRONICS CO.,LTD					
DRAWN	J.X.Zhang	2014/08/20	TITLE:	MULTIFUNCTIONAL SWITCHES				
CHECKED			PART NO.	EP-□□□□				
APPROVALS			TOLERANCES ARE	30~以上: ±0.30 10~30: ±0.20 5~10: ±0.15 ~ 5: ±0.10	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			