



No. of Ways	Ordering code	A	B	C	D	E	F	Cable		Outlet	
								Round max.	Round min.	Flat max.	Flat min.
09	DS 09	32.2	22.1	25.0	38.5	15.0	28.6	6	4	-	-
15	DS 15	39.8	26.1	33.3	48.0	15.0	34.1	7	5	-	-
25	DS 25	54.2	30.3	47.0	63.0	15.0	38.3	8	6	-	-
37	DS 37	70.7	38.2	63.5	79.0	15.0	46.2	-	-	7X16	5X16
50	DS 50	68.0	38.2	61.1	76.5	18.0	46.2	-	-	10X16	5X16

Characteristics:

- * Facility for side & top cable entry.
- * External cable clamp can be used for top or side cable entry.
- * Available with slide lock with 2 screws for retaining connector.

Material:

Hood: Flame retardant thermoplastic.
Screws & Slide lock : steel, Zinc plated.

Computer4\productscon\ELECTRONICS\DHDCU

TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.1	PLASTIC HOODS (FOR SLIDE LOCK)	DIMENSIONS IN MM	
		DATE	SIGN.
SCALE ~		DESIGN	08.04.10
		DRAWN	08.04.10
		CHKD.	
		APPD.	
		DRG. NO. DHDCU-018. A4.	
		SHEET 1 OF 1	