







A	V	Hz		EARTH HR. POS		EARTH HR. POS		EARTH HR. POS
CURRENT	VOLTAGE	FREQUENCY	2P+E		3P+E		3P+N+E	

## Socket Outlets

**CEE** **NORM**

<b>16</b> 	110	50 - 60	11302	4	113	4	1110	4
	240	50 - 60	11304	6	114	9	1111	9
	415	50 - 60	112	9	11306	6	11308	6
<b>32</b> 	110	50 - 60	11310	4	1116	4	1122	4
	240	50 - 60	11312	6	1117	9	1123	9
	415	50 - 60	1115	9	11314	6	11316	6
<b>63</b> 	110	50 - 60	1106	4	1125	4	1129	4
	240	50 - 60	1104	6	1126	9	1130	9
	415	50 - 60	1107	9	1127	6	1124	6



### Surface Mounting Socket Outlet

Top & Bottom Cable Entry

 Splashproof

16A = M20




32A = M25

63A = M40 Top / M32 Bottom

16A and 32A with screw terminals

63A with screw / clamp terminals and pilot contact


**Note:** This pilot contact should **NOT** be counted as a main 'pin'

<b>16</b> 	110	50 - 60	11303	4	1135	4	1141	4
	240	50 - 60	11305	6	1136	9	1142	9
	415	50 - 60	1134	9	11307	6	11309	6
<b>32</b> 	110	50 - 60	11311	4	1147	4	1153	4
	240	50 - 60	11313	6	1148	9	1154	9
	415	50 - 60	1146	9	11315	6	11317	6
<b>63</b> 	110	50 - 60	1156	4	1159	4	1163	4
	240	50 - 60	1157	6	1160	9	1164	9
	415	50 - 60	1158	9	1161	6	1112	6



### Surface Mounting Socket Outlet

Top & Bottom Cable Entry

 Watertight

16A = M20

32A = M25

63A = M40 Top / M32 Bottom




16A and 32A with screw terminals

63A with screw / clamp terminals and pilot contact

**Note:** This pilot contact should **NOT** be counted as a main 'pin'




Other voltages and frequencies are available on request. Contact CEE Norm UK for further details

A	V	Hz		EARTH REL. POS.		EARTH REL. POS.		EARTH REL. POS.
CURRENT	VOLTAGE	FREQUENCY	2P+E		3P+E		3P+N+E	

## Socket Outlets

# CEE NORM

125 	110	50 - 60	11436	4	11439	4	11445	4
	240	50 - 60	11437	6	11440	9	11446	9
	415	50 - 60	11438	9	11441	6	11447	6


125A with screw / clamp terminals and pilot contact


**Note:** This pilot contact should **NOT** be counted as a main 'pin'



### Surface Mounting Socket Outlet

Top M50 Cable Entry

 Watertight

125 	110	50 - 60		4		4		4
	240	50 - 60	11476	6		9		9
	415	50 - 60		9	11477	6	11479	6

125A with screw / clamp terminals and pilot contact


**Note:** This pilot contact should **NOT** be counted as a main 'pin'





### Surface Mounting Socket Outlet

Top M40 Cable Entry

Bottom 1x M40/M50

 Watertight



16 	240	50 - 60	1183	6				9
	415	50 - 60		9			1186	6
32 	415	50 - 60					11190	6

16A and 32A with screw terminals



### Surface Mounting Socket Outlet

 Splashproof

16 	240	50 - 60	13105	6				9
	415	50 - 60					13108	6
32 	415	50 - 60					13146	6

16A and 32A with screw terminals






### Panel Mounting Socket Outlet

 Splashproof

Suitable for commercial / laboratory type applications





Other voltages and frequencies are available on request. Contact CEE Norm UK for further details

A	V	Hz		EARTH REL. POS.		EARTH REL. POS.		EARTH REL. POS.
CURRENT	VOLTAGE	FREQUENCY	2P+E		3P+E		3P+N+E	

# Socket Outlets

# CEE NORM

<b>16</b> 	110	50 - 60	1216	4	1219	4	1225	4
	240	50 - 60	1217	6	1220	9	1226	9
	415	50 - 60	1218	9	1221	6	1227	6
<b>32</b> 	110	50 - 60	1228	4	1231	4	1237	4
	240	50 - 60	1229	6	1232	9	1238	9
	415	50 - 60	1230	9	1233	6	1239	6



## Panel Mounting Socket Outlet

 Splashproof  
20° Angle

<b>63</b> 	110	50 - 60	12134	4	12137	4	12138	4
	240	50 - 60	12135	6	1207	9	1208	9
	415	50 - 60	12136	9	1201	6	1202	6



## Panel Mounting Socket Outlet


 Splashproof  
15° Angle

<b>16</b> 	110	50 - 60	130	4	13015	4		
	240	50 - 60	131	6	13016	9		
	415	50 - 60	132	9	13017	6		



## Panel Mounting Socket Outlet

 Splashproof  
Straight



<b>16</b> 	110	50 - 60	1310	4	1313	4	1319	4
	240	50 - 60	1311	6	1314	9	1320	9
	415	50 - 60	1312	9	1315	6	1321	6

Note: 1310 & 1311 are the popular versions



## Panel Mounting Socket Outlet


 Splashproof  
Straight

<b>16</b> 	110	50 - 60	13000	4	1322	4	13003	4
	240	50 - 60	13001	6	1323	9	13004	9
	415	50 - 60	13002	9	1324	6	13005	6
<b>32</b> 	110	50 - 60	13006	4	13009	4	1331	4
	240	50 - 60	13007	6	13010	9	1332	9
	415	50 - 60	13008	9	13011	6	1333	6



## Panel Mounting Socket Outlet

 Splashproof  
Straight Flange 75 x 75 mm

<b>63</b> 	110	50 - 60	1306	4	1309	4	13140	4
	240	50 - 60	1307	6	1304	9	1305	9
	415	50 - 60	1308	9	134	6	136	6


16A and 32A with screw terminals

63A with screw / clamp terminals and pilot contact

Note: This pilot contact should **NOT** be counted as a main 'pin'




## Panel Mounting Socket Outlet

 Splashproof  
Straight





Other voltages and frequencies are available on request. Contact CEE Norm UK for further details

A	V	Hz		EARTH REL. POS.		EARTH REL. POS.		EARTH REL. POS.
CURRENT	VOLTAGE	FREQUENCY	2P+E		3P+E		3P+N+E	


# Socket Outlets

# CEE NORM



16 	110	50 - 60	1265	4	1268	4	1274	4
	240	50 - 60	1266	6	1269	9	1275	9
	415	50 - 60	1267	9	1270	6	1276	6
32 	110	50 - 60	1277	4	1280	4	1286	4
	240	50 - 60	1278	6	1281	9	1287	9
	415	50 - 60	1279	9	1282	6	1288	6



## Panel Mounting Socket Outlet

 Watertight

20° Angle


63 	110	50 - 60	12000	4	12003	4	12004	4
	240	50 - 60	12001	6	1205	9	1206	9
	415	50 - 60	12002	9	1200	6	129	6
125 	110	50 - 60	1299	4	12102	4	12106	4
	240	50 - 60	12100	6	12103	9	12107	9
	415	50 - 60	12101	9	12104	6	12108	6



## Panel Mounting Socket Outlet


 Watertight

15° Angle



16 	110	50 - 60	1356	4	1359	4	1365	4
	240	50 - 60	1357	6	1360	9	1366	9
	415	50 - 60	1358	9	1361	6	1367	6



## Panel Mounting Socket Outlet

 Watertight

Straight



16 	110	50 - 60	1371	4	1374	4	1380	4
	240	50 - 60	1372	6	1375	9	1381	9
	415	50 - 60	1373	9	1376	6	1382	6
32 	110	50 - 60	13023	4	13026	4	1368	4
	240	50 - 60	13024	6	13027	9	1369	9
	415	50 - 60	13025	9	13028	6	1370	6



## Panel Mounting Socket Outlet


 Watertight

Straight

63 	110	50 - 60	1395	4	1398	4	13102	4
	240	50 - 60	1396	6	1399	9	13103	9
	415	50 - 60	1397	9	13100	6	13104	6
125 	110	50 - 60	13445	4		4		4
	240	50 - 60	13452	6		9		9
	415	50 - 60		9	13447	6	13451	6



## Panel Mounting Socket Outlet

 Watertight

Straight

16A and 32A with screw terminals

63A and 125A with screw / clamp terminals and pilot contact

**Note:** This pilot contact should **NOT** be counted as a main 'pin'



Other voltages and frequencies are available on request. Contact CEE Norm UK for further details