

FTP Cat6 Patch cord, grey, 0.25 m

PP6-0.25M

- Perfect connection
- Foil shielded for a reliable connection
- Gold plated contacts



Features

- Foil shielded patch cord, 8P8C
- 50u" gold plated contacts
- Molded strain reliefs
- Snagless boots

Packaging

Q'ty in crtn, pcs	500
Crtn volume, CUM	0.04
Crtn weight, kgs	9.8
Individual package size LxWxH:	150x120x10 mm
Carton size LxWxH:	395x330x305 mm
Country of origin	CN
Barcode	8716309056199
Customs code	8544421000

Specifications

Patch cord category 6 FTP (shielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.86 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: 7 x 0.12 mm CCA
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Certificates

