


LED Signalleuchten LED Panel Mount Indicators

Standardreflektor 130/230V AC mit Berührungsschutzhülse IP67 / Standard bezel 130/230V AC with protection tube IP67



Part Number	Colour	Voltage	Typ. Current	Typ. Lumi. Intensity
Hochglanzverchromter Metallreflektor / Satin chrome bezel				
19350130	red	130V AC	6mA AC	47mcd
19350131	green	130V AC	6mA AC	34mcd
19350133	yellow	130V AC	6mA AC	27mcd
19350135	ultra-green	130V AC	6mA AC	660mcd
19350137	blue	130V AC	6mA AC	196mcd
1935013W	white	130V AC	4mA AC	700mcd
19350230	red	230V AC	3mA AC	18mcd
19350231	green	230V AC	3mA AC	11mcd
19350233	yellow	230V AC	3mA AC	8mcd
19350235	ultra-green	230V AC	3mA AC	330mcd
19350237	blue	230V AC	3mA AC	98mcd
1935023W	white	230V AC	2,5mA AC	440mcd
Schwarzverchromter Metallreflektor / Black chrome bezel				
19351130	red	130V AC	6mA AC	47mcd
19351131	green	130V AC	6mA AC	34mcd
19351133	yellow	130V AC	6mA AC	27mcd
19351135	ultra-green	130V AC	6mA AC	660mcd
19351137	blue	130V AC	6mA AC	196mcd
1935113W	white	130V AC	4mA AC	700mcd
19351230	red	230V AC	3mA AC	18mcd
19351231	green	230V AC	3mA AC	11mcd
19351233	yellow	230V AC	3mA AC	8mcd
19351235	ultra-green	230V AC	3mA AC	330mcd
19351237	blue	230V AC	3mA AC	98mcd
1935123W	white	230V AC	2,5mA AC	440mcd
Mattverchromter Metallreflektor / Matt chrome bezel				
19352130	red	130V AC	6mA AC	47mcd
19352131	green	130V AC	6mA AC	34mcd
19352133	yellow	130V AC	6mA AC	27mcd
19352135	ultra-green	130V AC	6mA AC	660mcd
19352137	blue	130V AC	6mA AC	196mcd
1935213W	white	130V AC	4mA AC	700mcd
19352230	red	230V AC	3mA AC	18mcd
19352231	green	230V AC	3mA AC	11mcd
19352233	yellow	230V AC	3mA AC	8mcd
19352235	ultra-green	230V AC	3mA AC	330mcd
19352237	blue	230V AC	3mA AC	98mcd
1935223W	white	230V AC	2,5mA AC	440mcd

Maximale Frontplattenstärke 11mm / Maximum panel thickness 11mm
Andere Spannungen auf Anfrage / Other voltages on request

EINBAUDURCHMESSER
MOUNTING HOLE

6 mm

8 mm

12 mm

14 mm

16 mm

19 mm

22 mm

ZUBEHÖR
ACCESSORIES