

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-55 °C TO 60 °C	
	VOLTAGE	V AC	OPERATING HUMIDITY RANGE	- % TO - %	
	CURRENT		APPLICABLE CABLE	MAX ϕ 6.7	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
MECHANICAL CHARACTERISTICS					
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2h FOR 3 DIRECTIONS.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms, AT 3 TIMES FOR 6 DIRECTIONS.		X	-	
ENVIRONMENTAL CHARACTERISTICS					
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Δ					
REMARK Unless otherwise specified, refer to JIS C 5402.			APPROVED	YH. ENAMI	08.12.09
			CHECKED	HO. MIWA	08.12.09
			DESIGNED	YH. MAMADA	08.12.08
			DRAWN	YH. MAMADA	08.12.08
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-040768-01	
HRS	SPECIFICATION SHEET		PART NO.	DX-20-CV1	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL230-0054-8-00	Δ 1/